

Dimensional Chart

						DIN 32676							
						Series A	Series B	Series C					
ID		OD		Bead		DIN11850/ DIN10357	ISO1127	ASME BPE	ISO 2852	SMS 3019	BS 4825-3	SCH 5 BS	Special Size
inch	mm	inch	mm	inch	mm								
0.17	4.20	0.86	21.80	0.80	20.20								X
0.19	4.80	0.86	21.80	0.80	20.20			1/4"					
0.24	6.20	0.86	21.80	0.80	20.20	DN06							
0.28	7.20	0.86	21.80	0.80	20.20		DN10.2						
0.31	8.00	0.86	21.80	0.80	20.20			3/8"					
0.32	8.20	0.86	21.80	0.80	20.20	DN08							
0.38	9.60	0.86	21.80	0.80	20.20			1/2"			1/2"		
0.41	10.50	0.86	21.80	0.80	20.20		DN13.5						
0.48	12.20	0.86	21.80	0.80	20.20								X
0.56	14.20	0.86	21.80	0.80	20.20		DN17.2						
0.63	16.00	0.86	21.80	0.80	20.20			3/4"			3/4"		
* Mini gaskets do not have a ferrule bead. Above sizes utilize clamp size: 13MHM-304-050/075													
0.39	10.00	1.34	34.00	1.08	27.50					DN12			
0.40	10.20	1.34	34.00	1.08	27.50	DN10			DN12				
0.41	10.50	1.34	34.00	1.08	27.50								DN13.5 ISO1127 with OD 34mm
0.43	10.90	1.34	34.00	1.08	27.50				DN12.7				
0.56	14.20	1.34	34.00	1.08	27.50								DN17.2 ISO1127 with OD 34mm
0.61	15.40	1.34	34.00	1.08	27.50				DN17.2				
0.64	16.20	1.34	34.00	1.08	27.50	DN15				DN18			
0.72	18.30	1.34	34.00	1.08	27.50								DN21.3 ISO1127 with OD 34mm
0.77	19.50	1.34	34.00	1.08	27.50				DN21.3				
0.80	20.20	1.34	34.00	1.08	27.50	DN20							
0.88	22.30	1.34	34.00	1.08	27.50								1" ASME BPE with OD 34mm
Above sizes utilize clamp size: 13MHM-304-34mm													
0.40	10.20	2.00	50.50	1.71	43.50								DN10 DIN11850 with OD 50.5mm
0.56	14.20	2.00	50.50	1.71	43.50								DN17.2 ISO1127 with OD 50.5mm
0.64	16.20	2.00	50.50	1.71	43.50								DN15 DIN11850 with OD 50.0mm
0.72	18.30	2.00	50.50	1.71	43.50		DN21.3						
0.80	20.20	2.00	50.50	1.71	43.50								DN20 DIN11850 with OD 50.5mm
0.88	22.30	2.00	50.50	1.71	43.50			1"					
0.90	22.80	2.00	50.50	1.71	43.50				DN25	DN25			
0.90	22.90	1.49	37.70	1.25	31.75								X
0.94	23.90	2.00	50.50	1.71	43.50		DN26.9						
1.03	26.20	2.00	50.50	1.71	43.50	DN25							
1.18	29.90	2.00	50.50	1.71	43.50		DN33.7						
1.20	30.50	2.00	50.50	1.71	43.50							1"	
1.24	31.50	2.00	50.50	1.71	43.50				DN33.7	DN33.7			
1.27	32.50	2.00	50.50	1.71	43.50	DN32							
1.38	35.00	2.00	50.50	1.71	43.50			1.5"			1.5"		
1.41	35.80	2.00	50.50	1.71	43.50				DN38	DN38			
1.50	38.20	2.00	50.50	1.71	43.50	DN40							
1.52	38.60	2.00	50.50	1.71	43.50								DN42.4 ISO1127 with OD 50.5mm
Above sizes utilize clamp size: 13MHM-304-100/150													
1.49	37.80	2.52	64.00	2.22	56.50				DN40				
1.52	38.60	2.52	64.00	2.22	56.50		DN42.4						
1.75	44.50	2.52	64.00	2.22	56.50		DN48.3						
1.78	45.30	2.52	64.00	2.22	56.50							1.5"	
1.88	47.70	2.52	64.00	2.22	56.50			2"			2"		
1.92	48.80	2.52	64.00	2.22	56.50				DN51	DN51			
1.98	50.20	2.52	64.00	2.22	56.50	DN50							
Above sizes utilize clamp size: 13MHM-304-200													

						DIN 32676							
						Series A	Series B	Series C					
ID		OD		Bead		DIN11850/ DIN10357	ISO1127	ASME BPE	ISO 2852	SMS 3019	BS 4825-3	SCH 5 BS	Special Size
inch	mm	inch	mm	inch	mm								
2.22	56.50	3.05	77.50	2.78	70.50		DN60.3						
2.26	57.40	3.05	77.50	2.78	70.50						2"		
2.38	60.40	3.05	77.50	2.78	70.50			2.5"		2.5"			
2.38	60.50	3.05	77.50	2.78	70.50				DN63.5	DN63.5			
Above sizes utilize clamp size: 13MHHM-304-250													
2.61	66.20	3.58	91.00	3.29	83.50	DN65							
2.64	67.00	3.58	91.00	3.29	83.50				DN70				
2.72	69.00	3.58	91.00	3.29	83.50						2.5"		
2.85	72.30	3.58	91.00	3.29	83.50		DN76.1						
2.88	73.10	3.58	91.00	3.29	83.50			3"	DN76.1	DN76.1	3"		
Above sizes utilize clamp size: 13MHHM-304-300													
3.20	81.20	4.17	106.00	3.82	97.00	DN80							
3.33	84.50	4.17	106.00	3.82	97.00		DN88.9						
3.35	85.10	4.17	106.00	3.82	97.00				DN88.9	DN88.9	3"		
Above sizes utilize clamp size: 13MHHM-V-304-300													
3.84	97.60	4.67	119.00	4.33	110.00			4"			4"		
3.85	97.80	4.67	119.00	4.33	110.00				DN101.6	DN101.6			
3.94	100.20	4.67	119.00	4.33	110.00	DN100							
Above sizes utilize clamp size: 13MHHM-304-400													
4.33	109.90	5.12	130.00	4.80	122.00		DN114.3						
4.35	110.50	5.12	130.00	4.80	122.00				DN114.3	DN114.3	4"		
Above sizes utilize clamp size: 13MHHM-V-304-400													
4.86	123.50	5.68	144.20	5.29	134.30			5**					
Above sizes utilize clamp size: 13MHHM-304-500													
4.93	125.20	6.10	155.00	5.75	146.00	DN125							
5.30	134.70	6.10	155.00	5.75	146.00		DN139.7						
5.35	135.90	6.10	155.00	5.75	146.00				DN139.7	DN139.7	5**		
Above sizes utilize clamp size: 13MHHM-V-304-500													
5.79	147.10	6.57	167.00	6.16	156.50			6"					
Above sizes utilize clamp size: 13MHHM-304-600													
5.91	150.20	7.20	183.00	6.85	174.00	DN150							
6.43	163.30	7.20	183.00	6.85	174.00		DN168.3		DN168.3	DN168.3	6"		
Above sizes utilize clamp size: 13MHHM-V-304-600													
7.78	197.60	8.56	217.40	8.15	207.00			8**					
Above sizes utilize clamp size: 13MHHM-304-800													
7.88	200.20	9.19	233.50	8.86	225.00	DN200							
8.43	214.10	9.19	233.50	8.86	225.00		DN219.1		DN219.1	DN219.1	8"		
Above sizes utilize clamp size: 13MHHM-V-304-800													
9.77	248.20	10.66	271.00	10.14	257.60	DN250*		10**					
Above sizes utilize clamp size: 13MHHM-V-304-1000													
10.49	266.50	11.32	287.60	11.00	279.40						10"		
11.81	300.00	12.56	319.00	12.17	309.00	DN300*		12**					
12.44	316.00	13.31	338.10	12.93	328.42						12"		
Above sizes utilize clamp size: 13MHHM-V-304-1200													

* Not included in the sanitary standard

